


Micro Date Stamp

mmE Q



Ideal for limited spaces due to their small size.

- Material is INOX.1.4034 48-54HRC
- Maximum working temperature is 150°C

Micro Date Stamp Assemblies (MDA) are supplied complete with (IU) Unit Insert, (AS) Support Unit, (AR) Retention Ring and (UM) Mounting Jig

Blank



12 Months/ Year



¹MDA031012-





MDA03101SF

Blank



IU031000

12 Months/ Year




¹IU031095-_

12 Months/ No Year



IU0310SF

(1) When ordering add the year required to the part number (MDA031012-06)



- 1 Machine pocket and mark reference point or line on cavity.
- 2 Insert Retention Ring (AR) with Mounting Jig (UM) position 1.
- 3 Drive fit Support Ring (AS) with Mounting Jig (UM) position 2.
- 4 Screw in the Unit Insert (IU).
- 5 Unscrew the Unit Insert (IU) to change the year.

CAD files and flash demo at:

CUMSA